

Constant Voltage LED Driver 24vdc 320 Watt



The RS Pro Range of 320watt Constant voltage LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications

Features:

- Input Voltage 90-305vac
- IP20 Rated
- Class II
- Compact Plastic Low Profile enclosure
- 1 Year Warranty
- CE Approved



ENGLISH

Specification

Part Number	1766736
Output Voltage Rating	22-27V DC
Output Current Range	6.7-13.4A
Rated Power	320W max
Dimensions	246 x 84 x 41.4 mm
Input Voltage Range	90-305vac
Input Voltage Frequency	47-63Hz
Inrush Current	45A/230V (25°C)
Efficiency	92%
Power Consumption Without Load	PF>0.95 (230V 50Hz) PF>0.98(115V 50Hz)
Overload Protection	1.1~1.6 times rated load (auto-recovery)
Short Circuit Protection	Hiccup mode auto-recovery
Automatically Restart	Yes
Working Temperature	-40-70C
Relative Humidity	15 -95%
MTBF	225Khrs MIL-HDBK-217F (25C)
EMC emission	EN55015,Fcc par15 Class B
EMC Immunity	EN61000-4-2,3,4,5,6,8,11; EN55024; EN61547
Safety Standards	EN61347-1, EN61347-2-13