



Brand of NTN corporation

Technical data

EXFE207

Bearing units




Grey cast housing, radial insert ball bearing with eccentric locking collar, seal with slinger

KIT CONTENT

EX207G2, FE207

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
A - Housing height	36 mm
A1 - Housing foot height / flange height	12,5 mm
A2 - Total height from mounting surface	53,3 mm
B - Width of Inner Ring	37,6 mm
B1 - Overall width Inner Ring	51,1 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

d - Shaft diameter	35 mm
d1 - Outer dia of eccent. Lock. collar / nut of adapter sleeve	51,1 mm
e - Distance mounting surface to bearing center	21 mm
G - Grease fitting	R1/8"
J - Mounting holes distance	92 mm
L - Housing width / diameter	118 mm
N - Mounting hole dimension	14 mm
S - Distance front side/bearing centre	18,8 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	25700000 mN
C0 - Static load rating	15200000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	1,7 kg
Recommended tightening torque for set screw	11.5 N-m

