


Classic LED Lamps

CLA LEDBulb D 7.5-60W A60 B22 827 CL



Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

PHILIPS

Product data

• General Information

Cap-Base	B22
Bulb Shape	A60 [A 60mm]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
B50L70	15000
Technical Type	7.5-60W

• Light Technical

Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	806 lm
Luminous Flux (Rated) (Nom)	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	107.47 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

• Operating and Electrical

Power (Rated) (Nom)	7.5 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s

Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V

• Controls and Dimming

Dimmable	Yes
----------	-----

• Mechanical and Housing

Bulb Finish	Clear
-------------	-------


• Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	8 kWh

• Product Data



Full product code	871869657551200
Order product name	CLA LEDBulb D 7.5-60W A60 B22 827 CL
EAN/UPC - Product	8718696575512
Order code	929001228302
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001228302
Net Weight (Piece)	0.030 kg

Dimensional drawing



filament 7W-60W 806lm NAD 2700K B22D

Product	D	C
CLA LEDBulb D 7.5-60W A60 B22 827 CL	60 mm	110.5 mm



© 2016 Philips Lighting Holding B.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2016, September 14
data subject to change