



DWE6411

1/4 SHEET ORBITAL SANDER-

Selling Proposition

- 230 Watt motor sands at 14,000 orbits per minute, providing a superior finish
- Hook & loop platen allows faster paper change, better dust extraction and increase sanding efficiency
- Paper clamps provided for conventional abrasives
- Textured anti-slip top and body grip provides ultimate comfort and control during prolonged use
- Dust sealed switch for increased durability
- Sealed 100% ball-bearing construction provides longer life

Standard Equipment

- Dust bag with built-in extractor connection

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Input	230 Watts
Orbits Per Minute	14000 opm
Orbit Size	1.6 mm
Paper Size	140x115 mm
Pad Size	108x115 mm
Weight	1.1.28 kg
Length	160 mm