Lifting Slings



FEATURES

- Shock absorbing qualities
- Good wear resistance
- Safety hooks included
- Supplied with a Test Certificate
- Chains resist abrasions

RS PRO 2m Lifting Sling Chain, 1.6t

RS Stock No.: 674-162



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Lifting Slings



Product Description

RS PRO Chain lifting slings provides excellent shock absorption and good wear resistance with 2 and 4 leg load capacities. The chain slings are shot blasted, protected plus all self- coloured and include safety hooks. Various end fittings and sling types are available as are lengths and widths of the chain lifting slings

General Specifications


Sling Type	Bridle Sling	
Safe Working Load (2-Leg)	1.6t	
Safe Working Load (4-Leg)	1.1t	
Applications	Lifting heavy loads	


Mechanical Specifications

Length	2000mm
Width	7mm
End Fittings	Hook to Eye


Lifting Slings







Two Leg $\beta = 0 \text{ to } 45^{\circ} \quad \beta = 45 \text{ to } 60^{\circ}$ Factor 1.4 Factor 1



β = 0 to 45°	= 45 to 60°
Factor 2.1	Factor 1.5