

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **Flanged Design:** Facilitates easy installation and alignment.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads.
- **ISO 2795 and ISO 9001:2008 Certified:** Ensures quality and compliance with international standards.

RS PRO 38.03 mm Flanged Plain Bearing

RS Stock No: 558-498



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 38.03 mm Flanged Plain Bearing is designed for applications requiring reliable rotational movement with minimal friction. Ideal for use in machinery where space constraints are a concern, this bearing ensures smooth operation and longevity.

General Specifications

Bore Size	38.03 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	48.06 mm
Width	35 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

