


KEMET Part Number: SSRH24NV-45059
(UALS24V4505900)

KEMET, SSRH24NV/NH, AC Line Filters, Common Mode, 5900 uH



Dimensions

L	25.5mm MAX
T	20mm MAX
H	31mm MAX
LL	3.5mm +/-0.5mm
S	13mm NOM

Packaging Specifications

Packaging:	Tray
Packaging Quantity:	240
Weight:	25 g

General Information

Series:	SSRH24NV/NH
Style:	Through-Hole
Features:	Compact Size, Light Weight, Low Rdc, Ultra-High Impedance
RoHS:	Yes
Miscellaneous:	Temperature Rise Maximum: 65 K

Specifications

Voltage AC:	250 VAC
Inductance:	5.9 mH (10 kHz)
Current:	4.5 A
Temperature Range:	-25/+120°C
DC Resistance:	48 mOhms