



ENGLISH

European 2-Pin Plug-in top Power Supply 24vdc 15watt



The RS Pro Range of Class II 15watt AC/DC European plug-in power supplies provide 15 watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications.

Features:

- European Fixed AC Head
- 3 Year Warranty
- Level VI Efficiency
- CE Approved





ENGLISH

Specification	
RS Stock Number	1753318
Input Voltage Range	90-264Vac
Input Frequency Range	47-63Hz
Input Current Rated	0.5A Max
Output Voltage Rating	+24V
Output Current Range	0A
Output Min Current	0.625A
Output Connection Type	2.1x5.5x12mm Centre Positive – Straight
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 2%
Ripple & Noise	300mVp-p
Efficiency	80.59% Min
Over Voltage Protection	26.5vdc Max
Over Load Protection	>0.76A
Operating Temperature	0 to 40°C
Storage Temperature	-20 to +60°C
Operating Humidity	20 to 85%
Storage Humidity	5 to 95%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	T-LICENSE(BS EN60950-1)
EMI Standard	CE(EN55022)
MTBF	50K Hours
Size mm max.	74.5 (L) 50.9 (W) * 84.4(H)
Weight	120 +/-30%
Regulator Type	Switched Mode Power Supply