

Product Datasheet

XVR111SCC

witty one charging station 1x11kW 3ph+N Type 2S socket for company vehicle

Technical characteristics	
Power	Max. power per charging point: 11 kW Connected power: 0.1 - 11 kW
Frequency	50 - 60 Hz
Power supply	Number of supply phases: 3
Electric current	Rated current IN: 16 A
Connectivity	Number of charging points: 1
Functions	Load management: No
Equipment	Domestic sockets: 0 Protective circuit breaker: No Emergency trip on power failure: Yes
Connection	Connector/socket type: Type 2S
Dimensions	370 x 250 mm Height: 370 mm Width: 250 mm Depth: 150 mm
Installation	Wall mounting
Safety	IP55 Impact resistance IK10
Operating conditions	Operating temperature: -25 to 50 °C
Voltage	Rated voltage: 400 - 400 V
Material	Plastic

Photos | Drawings

Translated English version of the original Hager datasheet.