

eco!Booster TR 080

eco!Booster with 50% higher area performance than the Kärcher power nozzle; ideal for delicate surfaces. For cold and hot water high-pressure cleaners (nozzle size 080).



Order no. **2.113-089.0**

Technical data

EAN code		4066529118868
Pressure	bar	max. 300
Temperature	°C	max. 85
Nozzle size		80
Connection thread		EASY!Lock
Weight incl. packaging	kg	0.5



50% higher cleaning performance compared to the flat jet

- Thorough, fast and more sustainable cleaning.

50% higher water efficiency*

- Saves water.
- * Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

50% higher energy efficiency*

- Saves energy.
- * Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

COMPATIBLE MACHINES

- HD 10/25-4 S