

Product datasheet

Specifications



APC Easy Rack, 24U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, 1198H x 600W x 800D mm

ER6482

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or component type	Rack
Number of rack unit	24U
Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels

Physical

Height	119.8 cm
Width	60 cm
Depth	80 cm
Net weight	68.4 kg
Colour	Black
Maximum mounting depth	64.14 cm
minimum mounting depth	19.05 cm
Rack width	19"
Marking	18 gauge front door 19 gauge rear door 16 gauge post 14 gauge EIA mounting rail
Permanent permissible load	1199.8 kg static 599.6 kg

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	133 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	65 cm
Package 1 Length	85 cm
Package 1 Weight	74 kg

Contractual warranty

Warranty	2 Years repair or replaceNote- extended warranty options are available
----------	--

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	225

Use Better	
Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
[EU RoHS Directive](#)	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	[REACH Declaration](#)
Use Again	
Repack and remanufacture	
Circularity Profile	[End of Life Information](#)
Take-back	No