



Fuse-link, LV, 224 A, AC 500 V, NH1, gL/gG, IEC, dual indicator, live gripping lugs

**Catalog No.** 224NHG1B

**EL-Nummer (Norway)** 0001664055

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	224
Rated voltage			AC 500 V
Construction size			NH1
Utilization category			gL/gG
Status indicator			dual (combination) indicator system
Description			live gripping lugs
Breaking Capacity		kA	120
Standard/Approval			IEC
Shape			square body with knife blade contacts
Standards/Regulations			IEC 60269-2 fuse system A DIN 43620 VDE 0636-2

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			NH1
Rated current		A	224
Rated voltage		V	500
Voltage type			AC
Rated switching capacity		kA	120
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			Combination fuse status indicator
Insulated metal gripping lugs (IMGL)			No

### Additional product information (links)

Product datasheet (pdf)	<a href="http://www1.cooperbusssmann.com/pdf/dd9b7025-0e58-46b4-b717-66ce5e12c2b8.pdf">http://www1.cooperbusssmann.com/pdf/dd9b7025-0e58-46b4-b717-66ce5e12c2b8.pdf</a>
-------------------------	---