

REV.	MODIFICATION.	DATE	DRN
01	NEW DRAWING	22/10/04	NJB
02	ECN 04-219	09/12/04	NJB
03	ECN 05-061	11/05/05	OW
04	ECN 06-253	24/11/06	OW
05	ECN 07-089	25/05/07	SF
06	CO-2010422	03/10/08	OW
07	CO-2010547	18/02/09	SF
08	CO-2010940	10/06/10	SF
09	CO-2010979	31/08/10	SF
10	CO-2011201	27/09/11	SF
11	CO-2011253	12/04/12	SF





FIG 1





FIG 2

NOTES:

- 1) ALL LENGTHS ARE AVAILABLE IN 1mm INCREMENTS.
- 2) PARTS AVAILABLE IN NYLON 6 GF25% V-0 (RMS-205), COLOUR NATURAL (MAY APPEAR BROWN) BY SPECIAL ORDER. TO ORDER ADD "V" TO THE END OF THE PART NUMBER. EXAMPLE: "HNSM2-20-5-1V"


ALTERNATE UNITS FOR REFERENCE ONLY

PART NO.	D1=D2	H	L		FIG
HNSM2-L-5-1	M2	5[.197]	5-10[.197-.394]	11-45[.433-1.77]	2
HNSM2.5-L-5-1	M2.5		4-10[.158-.394]	11-55[.433-2.2]	2
HNSM3-L-5.5-1	M3	5.5[.22]	5-10[.197-.394]		1
HNSM3-L-6-1		6[.24]	5-15[.197-.591]	2	
HNSM3-L-7-1		7[.276]	5-15[.197-.591]		
HNSM3-L-8-1		8[.32]	6-15[.237-.591]		
HNSM4-L-8-1	M4	10[.394]	5-20[.197-.788]	21-68[.827-2.678]	1
HNSM4-L-10-1			10-20[.394-.788]	21-60[.827-2.363]	
HNSM5-L-10-1	M5	10[.394]	5-20[.197-.788]	21-65[.827-2.56]	2
HNSM6-L-10-1	M6		10-20[.984-.788]	21-60[.827-2.363]	
		P1=P2	THROUGH	10[.394] MAX	



METRIC GENERAL TOLERANCES ±0.25
ARE PRIMARY UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°

IMPERIAL GENERAL TOLERANCES ±0.010
ARE FOR REFERENCE UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°

MATERIAL: NYLON 6 25% GF (RMS-173)		COLOUR: BLACK (SEE NOTE 2)	
TITLE: HEXAGONAL THREADED SPACER, NYLON		PART No: HTSN-MD-L-H-1	
DRG No: 04-130	NPR REF: N/A		SIZE A4
DRN NJB	DATE 22/10/04	CHKD RC	DATE 23/10/04
SCALE NTS		SHEET No 1 OF 1	