

Querschnitt/Cross-section [mm ²]	2,5	4	6	10	16	25	35	50	70	95	120	150	185	240
Reihenklemme/Terminal														
3076510 UKH 240-3L-F													se	se
3076594 UKH 240-3L/FE-F													se	se
3076552 UKH 240-3L/N-F													se	se
3076633 UKH 240-3L/N/FE-F													se	se
0707743 HDFK 25			re	re	re	re								
0707769 HDFK 25 GNYE			re	re	re	re								
0707785 HDFK 25-PE			re	re	re	re								
0709136 HDFK 25-VP			re	re	re	re								
0709149 HDFK 25-VP GNYE			re	re	re	re								
0709039 HDFKV 25			re	re	re	re								
0709042 HDFKV 25 GNYE			re	re	re	re								
0708962 HDFKV 25-VP			re	re	re	re								
0708739 HDFK 50							re	se						
0708726 HDFK 50 GNYE							re	se						
0709123 HDFK 50-VP							re	se						
0708991 HDFK 50-VP GNYE							re	se						
0708522 HDFKV 50							re	se						
0708548 HDFKV 50 GNYE							re	se						
0708580 HDFKV 50-VP							re	se						
0717403 HDFKV 50-VP BU							re	se						
0708797 HDFKV 50-VP GNYE							re	se						
0709534 HDFK 95									se	se				
0717584 HDFK 95 BU									se	se				
0709644 HDFK 95-F									se	se				
0709916 HDFK 95-F-VP									se	se				
0717665 HDFK 95-F-VP GNYE									se	se				
0717979 HDFK 95-VP									se	se				
0709547 HDFKV 95									se	se				
0709660 HDFKV 95-DP									se	se				
0709673 HDFKV 95-F									se	se				
3073348 UW 16			re	re	re	re								
3073487 UW 16-POT			re	re	re	re								
3073490 UW 16-POT/S			re	re	re	re								
3073351 UW 16/S			re	re	re	re								
3073419 UWV 16			re	re	re	re								
3073542 UWV 16-POT			re	re	re	re								
3073555 UWV 16-POT/S			re	re	re	re								
3073432 UWV 16/S			re	re	re	re								
3073364 UW 25			re	re	re	re	re							
3073500 UW 25-POT			re	re	re	re	re							
3073513 UW 25-POT/S			re	re	re	re	re							
3073377 UW 25/S			re	re	re	re	re							
3073445 UWV 25			re	re	re	re	re							
3073568 UWV 25-POT			re	re	re	re	re							
3073571 UWV 25-POT/S			re	re	re	re	re							
3073458 UWV 25/S			re	re	re	re	re							

re	rund, eindrätig, Klasse 1; freigegeben / round (circular), solid, class 1; tests passed
se	sektorförmig, eindrätig, Klasse 1, α=90°; freigegeben / sector-shaped, solid, class 1, α=90°; test passed

Kabelaufbau gemäß / Cable according to:

DIN VDE 0276 Teil/Part 603 (national)
IEC 60502-1 (international)

