



RS 2-PP10

Glass Tube Fuse, 2A, 5x20mm, Fast

Product Properties:

Voltage type	AC/DC
Connection type	Base
Release characteristic	Fast (F)
Rated current	2 A
Rated voltage	250 V
Optical defect indication	No
Model	Glass fuse
Max. current (I _{max})	2 A

Dimensions:

MOQ	10 .
Unit	pck
Rated voltage	250 V
Dimensions	5x20 mm

Approvals:

Voltage type	AC/DC
--------------	-------

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Contain no Iron or Steel
REACH	No SVHC (247 Subs. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC002704 - Cylindrical fuse
ETIM-Release	9.0
Trademark	NECORE
Product Group	Glass tube fuses - Consumer pack
Search Description	GLASSÄKRING, 2A
Alternative SKU	RS2-PP10

Logistic information:

Barcode	733117640871
Country of origin	FR
Item status	Non Stock Item, can be on stock but is not a regular stock item.
MOQ	10 .
Stock code	RS 2-PP10
Taric code	85361010
Unit	pck

*We reserve the right to make technical changes and disclaim any typographical errors.