

Datasheet

10 - 22.5 mm Cone Cutter

RS Stock number [221-585](#)



Description:

A high speed, Steel tapered cone cutter, with a bright finish, for use with power tools for drilling clean holes in plastic, PC boards, alloys and sheet metal up to 2 mm thick.

It has a shank length of 22 mm.

No pilot hole is required.

Specifications:

Material: HSS

Maximum Drilling Thickness: 2 mm

Maximum Head Size: 22.5 mm

Minimum Head Size: 10 mm