

## 30 IMU-10

### Socket set 3/8"

26 pieces

Code  
6229740

ETIM  
EC002209

EAN  
4010886622971

UNSPSC  
27-11-17-03

Country of origin  
Germany

eCl@ss  
21-04-02-05

Customs tariff number  
82042000



**10** **3/8"** **mm**

### Article description

- With forged, tempered hexagon UD profile sockets, hand-operated
- With accessories made from GEDORE vanadium steel 31CrV3
- Set U-10 with reversible lever change ratchet
- In GEDORE blue sheet steel case
- Dimensions: 320 x 210 x 55 mm

### Article parts list

Reversible ratchet 3/8" No. 3093 U-10 200 mm, Cross handle 3/8" No. 3087, Extension 3/8" No. 3090-5 125 mm, Extension 3/8" No. 3090-10 250 mm, Cardan joint 3/8" No. 3095 51 mm, Socket wrench insert 3/8" No. 30 hexagon 6 7 8 9 10 11 12 13 14 15 16 17 19 mm, Screwdriver bit socket 3/8" No. 15 30 slot 5,5x1 8x1.2 mm, Screwdriver bit socket 3/8" No. 1N 30 hexagon socket 4 5 6 mm, Screwdriver bit socket 3/8" No. 1K5 30 Phillips PH 2 3

### Article information

Contents (Qty of pieces)	26	Total height [mm]	55 mm
Net weight [kg]	3.1 kg	Drive connector square female (metric)	10,0 mm
Total length [mm]	320 mm	Drive connector square female [inch]	3/8"
Total width [mm]	210 mm		