


FEATURES

- Durable 310
 stainless steel probe
 sheath for
 protection against
 corrosion and
 oxidation
- IEC 584 class 1 tolerance for optimum accuracy
- Mineral insulation for flexibility, durability and high performance
- Insulated hot junction for reduction in electrical interference
- Plain pot seal with a temperature rating of 200°C.

RS PRO Type K Thermocouple 500mm Length, 1.5mm Diameter → +1100°C

RS Stock No.: 787-7719



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Thermocouples



Product Description

From RS Pro a range of type K thermocouple temperature sensors that conform to IEC 584 standards with class 1 tolerance for optimum accuracy. These sensors or probes have a durable construction and feature a stainless steel 310 probe sheath and a PFA insulated lead. The mineral insulated flexible probe sheath can be bent and formed to suit a wide range of applications. The thermocouple has a single element insulated hot junction for a reduction in electrical interference and a plain pot seal with a temperature rating of 200°C.

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	-40°C to +1100°C
Construction	Flexible mineral insulated probe with stainless steel sheath, plain pot seal & 1 metre extension cable
Measuring Junction	Single element, junction insulated from sheath
Application	Heat exchangers, power stations, brick and cement kilns, heat treatment and annealing furnaces, thermostats, food thermometers, vehicle diagnostics and in laboratories.

Mechanical Specifications


Probe Diameter	1.5mm
Probe Length	500mm
Probe Body Material	Stainless Steel
Termination Type	Cable
Compensating Cable Length	1m

Approvals

Compliance/Certifications	IEC 584		
Standards Met	IEC		

Thermocouples





T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire code	Allied Code	RS order Code
'K'	1/0.2mm	1 metre	Mini plug	Green	White	70643600	363-0250
'K'	1/0.2mm	2 metre	Mini plug	Green	White		110-4482
'K'	1/0.2mm	5 metre	Mini plug	Green	White		123-6306
'K'	1/0.2mm	10 metre	Mini plug	Green	White		123-6307
')' ')' ')'	1/0.2mm 1/0.2mm 1/0.2mm 1/0.2mm	1 metre 2 metre 5 metre 10 metre	Mini plug Mini plug Mini plug Mini plug	Black Black Black Black	White White White White	70643599	363-0244 123-6308 123-6309 123-6310
'T'	1/0.2mm	1 metre	Mini plug	Brown	White	70643601	363-0266
'T'	1/0.2mm	2 metre	Mini plug	Brown	White		123-6311
'T'	1/0.2mm	5 metre	Mini plug	Brown	White		123-6312
'T'	1/0.2mm	10 metre	Mini plug	Brown	White		123-6313



	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Exten						
KX	7/0.2mm	+Green/-White	Green	10 metres	70657084	827-5615
KX	7/0.2mm	+Green/-White	Green	25 metres	70641729	236-3820
KX	7/0.2mm	+Green/-White	Green	50 metres	70657085	827-5619
KX	7/0.2mm	+Green/-White	Green	100 metres	70646156	611-7889
KX	7/0.2mm	+Green/-White	Green	200 metres	70657088	827-5628
		,				
JX	7/0.2mm	+Black/-White	Black	10 metres	70641640	219-4753
JX	7/0.2mm	+Black/-White	Black	25 metres	70657078	827-5592
JX	7/0.2mm	+Black/-White	Black	50 metres	70657079	827-5596
JX	7/0.2mm	+Black/-White	Black	100 metres	70641737	236-3915
JX	7/0.2mm	+Black/-White	Black	200 metres	70657081	827-5606
TX	7/0.2mm	+Brown/-White	Brown	10 metres	70641637	219-4703
TX	7/0.2mm	+Brown/-White	Brown	25 metres	70641734	236-3870
TX	7/0.2mm	+Brown/-White	Brown	50 metres	70657095	827-5653
TX	7/0.2mm	+Brown/-White	Brown	100 metres	70651749	762-1146
TX	7/0.2mm	+Brown/-White	Brown	200 metres	70657098	827-5662
NX	7/0.2mm	+Pink/-White	Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-White	Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-White	Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-White	Pink	100 metres	70657092	827-5640
	- /					J=

	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Compensating:						
VX (KCB)	7/0.2mm	+Green/-White	Green	10 metres	70657082	827-5609
VX (KCB)	7/0.2mm	+Green/-White	Green	25 metres	70641629	219-4551
VX (KCB)	7/0.2mm	+Green/-White	Green	50 metres	70657080	827-5603
VX (KCB)	7/0.2mm	+Green/-White	Green	100 metres	70641630	219-4573
VX (KCB)	7/0.2mm	+Green/-White	Green	200 metres	70657083	827-5612
VX (KCB)	13/0.2mm	+Green/-White	Green	10 metres	70657086	827-5621
VX (KCB)	13/0.2mm	+Green/-White	Green	25 metres	70657087	827-5625
VX (KCB)	13/0.2mm	+Green/-White	Green	50 metres	70657090	827-5634
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	70651750	762-1152
U (RCA)	7/0.2mm	+Orange/-White	Orange	10 metres	70657096	827-5656
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	70646158	611-7902
U (RCA)	7/0.2mm	+Orange/-White	Orange	50 metres	70657097	827-5659
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	70641641	219-4769
U (RCA)	13/0.2mm	+Orange/-White	Orange	25 metres	70657093	827-5643
U (RCA)	13/0.2mm	+Orange/-White	Orange	50 metres	70657094	827-5647
	-	-	_			

Thermocouples



T/C Type	Conductors	Cores	Reel Length	Allied code	RS order code
KX	1/0.2mm	+Yellow/-Red	25 metres	70656106	814-0030
KX	1/0.2mm	+Yellow/-Red	50 metres	70656111	814-0049
KX	1/0.2mm	+Yellow/-Red	100 metres	70656109	814-0042
KX	7/0.2mm	+Yellow/-Red	25 metres	70656110	814-0046
KX	7/0.2mm	+Yellow/-Red	50 metres	70656113	814-0055
KX	7/0.2mm	+Yellow/-Red	100 metres	70656114	814-0058
KX	1/0.3mm	+Yellow/-Red	25 metres	70656104	814-0024
KX	1/0.3mm	+Yellow/-Red	50 metres	70656107	814-0033
KX	1/0.3mm	+Yellow/-Red	100 metres	70656108	814-0036
TX	1/0.3mm	+Blue/-Red	25 metres	70656121	814-0080
TX	1/0.3mm	+Blue/-Red	50 metres	70656126	814-0099
TX	1/0.3mm	+Blue/-Red	100 metres	70656124	814-0092
TX	1/0.2mm	+Blue/-Red	25 metres	70656125	814-0096
TX	1/0.2mm	+Blue/-Red	50 metres	70656128	814-0106
TX	1/0.2mm	+Blue/-Red	100 metres	70656129	814-0109

code	RS order	Allied code	Reel Length	Jacket	Cores	Conductors	T/C Type
							Extension:
8	814-0018	70656102	25 m	Yellow	+Yellow/-Red	7/0.2mm	KX
7	814-0027	70656105	100 m	Yellow	+Yellow/-Red	7/0.2mm	KX
0	814-0020	70656103	200 m	Yellow	+Yellow/-Red	7/0.2mm	KX
5	813-9995	70656096	25 m	Black	+ White/-Red	7/0.2mm	JX
5	814-0005	70656098	100 m	Black	+ White/-Red	7/0.2mm	JX
8	814-0008	70656099	200 m	Black	+ White/-Red	7/0.2mm	JX
4	814-0074	70656119	25 m	Blue	+Blue/-Red	7/0.2mm	TX
3	814-0083	70656122	100 m	Blue	+Blue/-Red	7/0.2mm	TX
6	814-0086	70656123	200 m	Blue	+Blue/-Red	7/0.2mm	TX
						ng:	Compensatir
3	814-0103	70656127	25 m	Yellow	+Yellow/-Red	7/0.2mm	VX (KCB)
2	814-0112	70656130	100 m	Yellow	+Yellow/-Red	7/0.2mm	VX (KCB)
5	814-0115	70656131	200 m	Yellow	+Yellow/-Red	7/0.2mm	VX (KCB)
7 0 5 5 8 4 3 6	814-0027 814-0020 813-9995 814-0005 814-0088 814-0083 814-0103 814-0103	70656105 70656103 70656096 70656098 70656099 70656119 70656122 70656123	100 m 200 m 25 m 100 m 200 m 25 m 100 m 200 m	Yellow Yellow Black Black Black Blue Blue Blue Yellow	+Yellow/-Red +Yellow/-Red + White/-Red + White/-Red + White/-Red +Blue/-Red +Blue/-Red +Blue/-Red +Yellow/-Red	7/0.2mm	KX KX JX JX JX TX TX TX TX Compensatir VX (KCB) VX (KCB)



T/C Type	Conductors	Cores	Reel Length	Allied code	RS order code
J	1/0.2mm	+Black/-White	25 metres	70657194	827-5980
J	1/0.2mm	+Black/-White	50 metres	70657195	827-5984
J	1/0.315mm 1/0.315mm	+Black/-White +Black/-White	25 metres 50 metres	70657198 70657199	827-5993 827-5996
K	1/0.315mm	+Green/-White	25 metres	70657200	827-6000
K	1/0.315mm	+Green/-White	50 metres	70657205	827-6019
Т	1/0.315mm	+Brown/-White	25 metres	70657208	827-6028
Т	1/0.315mm	+Brown/-White	50 metres	70657206	827-6022
J	1/0.508mm	+Black/-White	25 metres	70657197	827-5990
J	1/0.508mm	+Black/-White	50 metres	70657201	827-6003
K	1/0.508mm	+Green/-White	25 metres	70657203	827-6012
K	1/0.508mm	+Green/-White	50 metres	70657204	827-6016
J	7/0.2mm	+Black/-White	25 metres	70657202	827-6006
K	7/0.2mm	+Green/-White	25 metres	70657207	827-6025
T	7/0.2mm	+Brown/-White	25 metres	70657209	827-6031
N	7/0.2mm	+Pink/-White	25 metres	70657210	827-6034