

Features

- Conductor Material: 100% copper wires
- Jacket Material: PVC, Black
- Cable Length: 1M
- Easy to install and reliable connection
- Color: Black

RS PRO DC Cables

RS Stock No.: 658292



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This 90-degree right angle plug can easily go through a narrow gap, will never bend and damage the power supply cord. This cable is suitable for CCTV security cameras, DVRs, surveillance monitoring systems, LED lights or other 2.1*5.5mm DC power equipment, etc.

Current: 3A.

Voltage: 12V.

Material: 2*0.5mm² copper wire.

Polarity distinction: brown positive, blue negative.

Connector 1: DC 5.5mm x 2.1mm x 9.5mm male right angle 90 degree.

Connector 2: bare wire with terminal crimped

General Specifications

Connector A	Male DC5.5*2.1*9.5mm
Connector A Gender	Male
Connector B	Open, terminal crimped
Connector Style	Plug, right angle
Outer Sheath Material	PVC
Sheath Colour	Brown, blue
Connector Plating	Nickel

Electrical Specifications

Connection	Open end cable
Voltage Rating	12V DC
Maximum Power	3A

Mechanical Specifications

Length	1m
Cable Specification	2*0.5mm ² copper wire

Operation Environment Specifications

Operating Temperature	0°C to 70°C
Storage Temperature	0°C to 70°C

Approvals

Standards Met	RoHS, Reach
Declarations	RoHS, Reach

