

Router - FL MGuard SMART2 - 2700640

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Router with intelligent firewall, up to 99 Mbps data throughput (wire speed performance), stateful inspection firewall for maximum security and extremely easy configuration



The figure shows a version of the product

Product Description

Small
The mGuard smart from Innominate features maximum possible security and performance in a minimum amount of space. It has never been easier to protect critical company computers, machines or any other IP connection reliably and securely from attacks.

Strong
The mGuard smart security appliance combines the extremely powerful mGuard hardware platform with proven mGuard firmware. Based on a robust embedded Linux system from Innominate, this combination integrates four perfectly coordinated security components: a bidirectional stateful firewall, a flexible NAT router, and industrial protection against malware as an option.

Smart
With its rugged housing and uncomplicated power supply via any USB port, the mGuard smart is the ideal solution for the mobile protection of critical company resources. Changes to the location and infrastructure can be implemented quickly and inexpensively.


Focus on security
The mGuard smart is particularly suitable for the mobile and stationary protection of workstations and environments close to the production process with low requirements for industrial hardening.

Your advantages

- Supply via USB



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 613842
GTIN	4046356613842
Weight per Piece (excluding packing)	185.200 g
Custom tariff number	85176200
Country of origin	Germany
Note	Made to Order (non-returnable)

Router - FL MGuard SMART2 - 2700640

Technical data

Dimensions

Width	77 mm
Height	27 mm
Depth	115 mm

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 % (non-condensing)

Interfaces

Interface	Ethernet
No. of ports	2 (RJ45)
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 Mbps
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity

Function

Basic functions	Firewall/router for office use or mobile service technicians
Supported browsers	HTTPS support required
Processor	Freescale processor with 300 MHz clocking
Status and diagnostic indicators	LEDs: In combination for boot process, heartbeat, system error, Ethernet status, recovery mode
Signal contact control current	500 mA (via USB interface or external power supply unit as an option)

Security functions

Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Network Time Protocol (NTP) client	Client
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Remote Syslog Logging	On external server
Virtual private network (VPN) throughput	max. 42 Mbps (Router mode, VPN bidirectional throughput) max. 27 Mbps (Stealth mode, VPN bidirectional throughput)
Number of VPN tunnels	0 (up to 250 tunnels with additional license as an option)
Encryption methods	DES, 3DES, AES-128, -192, -256
Data integrity	MD5, SHA-1, SHA 256, SHA-512
Firewall data throughput	max. 130 Mbps (Router mode, default firewall rules, bidirectional throughput) max. 61 Mbps (Stealth mode, default firewall rules, bidirectional throughput)
Firewall rules	Configurable stateful inspection firewall
Filtering	MAC and IP addresses, ports, protocols
Protection against	IP spoofing, DoS and Syn Flood Protection

Router - FL MGuard SMART2 - 2700640

Technical data

Security functions

Routing	NAT, 1:1-NAT, Port Forwarding
---------	-------------------------------

Network expansion parameters

Maximum conductor length (twisted pair)	100 m
-----------------------------------------	-------

Supply voltage

Supply voltage	5 V DC (from USB interface)
----------------	-----------------------------

General

Type AX	Stand-alone
Net weight	185.2 g
Housing material	Plastic

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	-------------------------------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19170405
eCl@ss 4.0	27240400
eCl@ss 4.1	27240400
eCl@ss 5.0	19030100
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170103
eCl@ss 8.0	19170103
eCl@ss 9.0	19170103

ETIM

ETIM 3.0	EC001423
ETIM 4.0	EC001478
ETIM 5.0	EC001478
ETIM 6.0	EC001478
ETIM 7.0	EC001478

UNSPSC

UNSPSC 6.01	20142601
-------------	----------

Router - FL MGuard SMART2 - 2700640

Classifications

UNSPSC

UNSPSC 7.0901	20142601
UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	43222609
UNSPSC 18.0	43222609
UNSPSC 19.0	43222609
UNSPSC 20.0	43222609
UNSPSC 21.0	43222609

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU*DE*08.B.00731/19
-----	--	---------------------

Accessories

Accessories

Configuration memory

Configuration memory - FL MEM PLUG - 2891259



Exchangeable configuration memory of the device settings for simple device exchange and set-up

Device parameterization

Router - FL MGuard SMART2 - 2700640

Accessories

Software - FL MGuard DM UNLIMITED - 2981974



Central device management software for MGuard devices for any number of devices in the field. For installation on a PC. No additional licenses required. Download trial version for up to 10 devices.

License

License - FL MGuard LIC LIFETIME FW - 2700184



License for lifetime software update of FL MGuard field devices.

License - FL MGuard LIC CIM - 2701083



License for activating CIFS Integrity Monitoring (CIM) on an FL MGuard

License - FL MGuard LIC VPN-250 GROUP - 2700192



License for up to 250 additional VPN online connections

License - FL MGuard LIC VPN-250 - 2700193



License for up to 250 additional VPN online connections

Router - FL MGuard SMART2 - 2700640

Accessories

License - FL MGuard LIC VPN-10 - 2700194



License for up to 10 additional VPN online connections

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250



Patch cable, CAT5, assembled, 0.3 m

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1 m

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

Router - FL MGuard SMART2 - 2700640

Accessories

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2 m

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3 m

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5 m

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10 m

Router - FL MGuard SMART2 - 2700640

Accessories

Patch cable - FL CAT6 PATCH 12,5 - 2891369



Patch cable, CAT6, pre-assembled, 12.5 m

Patch cable - FL CAT6 PATCH 15,0 - 2891372



Patch cable, CAT6, pre-assembled, 15.0 m

Patch cable - FL CAT6 PATCH 20,0 - 2891576



Patch cable, CAT6, pre-assembled, 20.0 m

Plug

RJ45 connector - FL PLUG RJ45 GR/2 - 2744856

RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve.



RJ45 connector - FL PLUG RJ45 GN/2 - 2744571

RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.



Protective cap

Router - FL MGuard SMART2 - 2700640

Accessories

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

Remote control software

License - MGuard SECURE VPN CLIENT LIC - 2702579



License for mGuard Secure VPN Client v11.x

SFP module

Media module - FL SFP LX - 2891767



Gigabit SFP module for transmission up to 30 km with a wavelength of 1310 nm.

Media module - FL SFP SX - 2891754



Gigabit SFP module for transmission up to 1 km with a wavelength of 850 nm.

Media module - FL SFP LH - 2989912



Gigabit SFP module for transmission up to 80 km with a wavelength of 1,550 nm.

Router - FL MGuard SMART2 - 2700640

Accessories

Media module - FL SFP FX - 2891081



The small form-factor plug-in module provides a fiber optic interface with a data transmission speed of 100 Mbps with a wavelength of 1310 nm (long).

Media module - FL SFP FX SM - 2891082



The small form-factor plug-in module provides a fiber optic interface with a data transmission speed of 100 Mbps with a wavelength of 1310 nm (long).

Assembly tool - FL CRIMPTOOL - 2744869



Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site
