

1/4" HEX SOCKETS - METRIC | E117295



Description

- ISO 2725-1 - DIN 3124 - ISO 1174-1 - ISO 1711-1 - ISO 691
- Chrome vanadium steel.
- OGV Profile: tightening torque applied to the sides rather than to the angles of the nut.
- High chrome finish.
- For manual use.

Information

EAN	3258951172957
------------	---------------

A [mm]	5,5
---------------	-----

d1 [mm]	12
----------------	----

d2 [mm]	8,8
----------------	-----

L [mm]	25
---------------	----

L1 [mm]	4.2
----------------	-----

Conditioning	10
---------------------	----

[g]	10
------------	----

