

568.3287-RW

INTERLOCKED SOCKET + RCD
32A 3P+N+E 6h 346-415V 60Hz 50Hz
136X390MM Screw terminals With
mechanical interlock



* Product image may be indicative



EN IEC 60309-1 (2022)
 EN IEC 60309-2 (2022)
 Low voltage direct. 2014/35/EU

■ GENERAL CHARACTERISTICS

Commercial Series	ADVANCE 2 Series
Synthetical description	INTERLOCKED SOCKET + RCD
Mounting version	SURFACE MOUNTING

■ TECHNICAL CHARACTERISTICS

Rated current	32A
Poles	3P+N+E
Hour position	6h
Rated voltage	346-415V
Working frequency	60Hz
	50Hz
Terminals	Screw terminals

■ PHYSICAL CHARACTERISTICS

Mounting version	SURFACE MOUNTING
Colour	RED
Material	THERMOPLASTIC
Protection degree	Watertight
Protection degree IP	IP66/IP67
Protection degree IK	IK07
Contact material	CuZn (brass)
Cable entry	DRILLING POINT MARK
Padlock	ø5mm

■ DIMENSIONAL CHARACTERISTICS

Flange	136X390MM
--------	-----------

■ DOWNLOAD

Technical drawing [PDF]
 Technical drawing [STP]
 Technical drawing [DWG]
 Wiring diagram
 Instruction manual
 Instruction manual

■ OPTIONS & VARIOUS NOTES

Options	With mechanical interlock
Notes	WITH DIN RAIL (6 MODULES)
Catalogue notes	Blank side with drilling point marks
	Cable gland included
	[LARGE] Possibility to enter from the bottom (smooth walls with drilling point mark)