



DC-DC Power over Ethernet Splitter POE14 Fully Compliant IEEE802.3af PD Power Supply



Features

- Fully Compliant IEEE802.3af DC Power Supply
- DC Good LED
- Non-Vented Case
- Gigabit Compatible
- Full Protection OTP, OCP, OVP
- 1 Year Warranty

Applications

- IP Telephones
- Wireless Network Access Points
- Blue Tooth Access Points
- Security Cameras
- IP Print Servers

Safety Approvals

- CE

Mechanical Characteristics

- Length: 100mm (3.94in)
- Width: 56mm (2.2in)
- Height: 28mm (1.1in)
- Weight: 0.2Kg (7.05oz)

Output Specifications

Model	DC Output Voltage	Output Current
POE14-033	3.3V	3.00A
POE14-050	5V	2.20A
POE14-120	12V	1.17A

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

INPUT:

Input Voltage Range

36 to 56V DC; Receives power from either data or spare pairs

Input Current

0.6A (DC) 36 V DC at maximum load

Inrush Current

0.4A maximum

OUTPUT:

Regulation

Line and Load ±5%

Ripple

12V model 120mVp-p
5 & 3.3V models 75mVp-p

Efficiency

72% (typical) at maximum load and 48V DC

Output Power

Output Model	Limit
3.3V	8.25W at 36-57V DC
5V	12.5W at 36-57V DC
12V	12W at 36-55V DC
12V	14W at 55-57V DC

ENVIRONMENTAL:

Temperature

Operation	0 to +40°C
Non-Operation	-25 to +65°C

Humidity

Operation	5 to 90%
-----------	----------

Immunity

ESD:	EN61000-4-2	Level 3
RS:	EN61000-4-3	Level 2
EFT:	EN61000-4-4	Level 2
Surge:	EN61000-4-5	Level 3
CS:	EN61000-4-6	Level 2
Voltage Dips:	EN61000-4-11	
Harmonic:	EN61000-3-2	

Note: CS, Surge, Harmonics and Dips tested with POE20U

EMC

EN55022 Class A

Dielectric withstand (HI-POT) Test

1500V AC for 1 minute, 10mA

Insulation Resistance

Primary to secondary: >10M Ohm 500V DC

FEATURES

Short Circuit Protection

Output can be shorted permanently without damage

Over Voltage Protection

By Zener clamping

Indicators

Green LED – Output Good

Input and Output Data Connector

RJ45

Warranty

1 Year

Output Connector

Center Positive Barrel 9mm x 2.5mm x 5.5mm
Tip is user changeable for other sizes

Dimension Diagram Unit: mm

