

Metric Size - TU

TU1610B-100

- Applicable tubing O.D.: Ø 2 to Ø 16 mm
- Operating temperature: -20 to 60 °C
- 29 colour variations.

Size	1610 (O.D. Ø16, I.D. Ø10)
Color	B (Black)
Roll Length	None
Reel Length	100 m
Suffix	None
-	Air, Water
Max. operating pressure at 20 °C	0.8 MPa
Weight	15.000 Kg

-
-

TU-29COLOR-A_EU.pdf