

Datasheet

RS Pro 1 Output, Plug In Power Supply, 12W, 2-Pin Euro Industrial



Features:

- Universal input
- No load power consumption $<0.3\text{W}$
- Energy efficiency level VI
- Compact and light-weight plastic case
- Protections: Short circuit/overload
- Class II power supply (without earth pin)
- Pass LPS
- UK and European versions available
- 1 year warranty

Specifications:

RS Stock No.		903-7026	903-7020	903-7039	903-7032	903-7036
Output	DC Voltage	5V	12V	15V	24V	48V
	Rated Current	2.4A	1A	0.8A	0.5A	0.25A
	Current Range	0-2.4A	0-1A	0-0.8A	0-0.5A	0-0.25A
	Rated Power	12W	12W	12W	12W	12W
	Line Regulation	±2% max.				
	Ripple & Noise	<10%				
Input	Voltage Range	90-264V ac				
	Frequency Range	47-63Hz				
	Efficiency	82%				
Protections	Short Circuit	Auto Recovery				
	Overload	Auto Recovery				
Environment	Working Temperature	0°C - 40°C				
Safety & EMC	Safety Standards	UL60950-1, TUV EN60950-1 Approved				
	EMC Emission	Compliance to EN55022 Class B, EN61000-3-2-3				
	EMC Immunity	Compliance to EN61000-2, 3, 4, 6, 8, 11				
Other	Dimensions	72*46*32mm (L*W*H)				

Mechanical Drawing:

UNIT: mm

