






FILE AMEND NOTE	DATE	REV.
ORIGINAL EDITION	MAR 25 2016	B/0



NOTE:

- 1.Electrical properties:**
 - 1.ALL COMPONENTS ARE RoHS COMPLIANT.
 - 2.100% OPEN AND SHORT TEST.
 - 3.CONDUCTOR RESISTANCE:3 OHMS
 - 4.INSULATION RESISTANCE:10 MEGOHMS.
 - 5.HI-POT:DC200V/0.01S
 - 6.PC TEST 4K*2K 60Hz PASS 1080P PASS

2. ROHS 2.0 and REACH

MODEL LIST

Model	Length
11.99.5601	1000mm
11.99.5602	2000mm
11.99.5603	3000mm
11.99.5605	5000mm

MATERIAL LIST

No.	PART NAME	DESCRIPTION	QTY	APPROVE BY	CHECK BY	DRAW BY	SCALE	MM
④	CABLE	(7/0.10BC*1P+7/0.10BC+ AM)* 5PCS+7/0.12BC*4C+AM+7/0.12BC+128/0.12 AL-MG+PVC, OD: 7.3±0.1mm, COLOR: BLACK	L			DP CABLE 4K*2K/ 60Hz		
③	OUTER MOLD	BLACK ABS	2	CUSTOMER		MAPE	TOLERANCE	
②	INNER MOLD	LD-PE	2	MODEL No.	11.99.560X-1~5M		X. ±1.00	X.X ±0.50
①	CONNECTOR	DisplayPort MALE , GOLD PLATED PIN, Nickel PLATED SHELL	2					
							PAGE	1/1