

Product information

87 01 560

KNIPEX Cobra® XXL

Pipe Wrench and Water Pump Pliers

DIN ISO 8976



- Greater gripping capacity but much lower weight than comparable pipe wrenches
- Fast push-button adjustment directly on the workpiece, no unintentional slipping of the joint
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	87 01 560
EAN	4003773044321
Pliers	grey atramentized
Head	polished
Handles	plastic coated
Weight	2,780 g
Dimensions	560 x 103 x 29 mm
Standard	DIN ISO 8976
REACH compliant	no
RohS compliant	no

Technical details

Adjustment positions	20
Capacities for nuts	Ø 4 1/2 Inch
Capacities for nuts	120 mm
Capacities for pipes (diameter)	Ø 115 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112

Spare Parts

87 09 560	Range of spare parts adjustment for 87 560,
-----------	---

technical change and errors excepted

