

# Data sheet

Hot air tool

## HG 2320 ESD

EAN 4007841020811



### Function description

### Technical specifications

Output	2300 W
Temperature	80 – 650 °C
Airflow rate	150 – 500 l/min
Temperature setting	in 10°C steps by joystick
Temperature display	LCD display
Heating element	Ceramic heating element
Residual heat indicator	Yes
Function, hanger	Yes
Restart protection	No
Thermal cut-out	Yes
Thermostat	Yes
Protection class (without earth terminal)	II
Dimensions (L x W x H)	253 x 87 x 200 mm
Mains power supply	230 V, 50 / 60 Hz
PU1, net weight	1,044 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841020811