

secvest.®

FU8007

Secvest 2WAY Base Kit (UK, DK, IT)

The Secvest 2WAY is the high-end wireless alarm center from ABUS Security-Center, setting new design and function standards with a maximum range of functions, bidirectional wireless control elements and innovative backlight function.

The basic kit provides all important components for effective protection and can be extended at any time, if required. For installation, 48 zones for wireless detectors and two lines for wired detectors are available. Communication between the center and the individual components works on 868.6625 MHz, a radio frequency that is reserved exclusively for security purposes. Up-to-date frequency-modulated wireless technology with millions of codes and duplex antenna technology guarantee reliable transmission of signals and quick and easy installation of the system and its components. Depending on structural conditions, the wireless coverage is approx. 30 meters indoors and up to 100 meters outdoors.

The system can easily be expanded at any time with additional or new components (wireless glass breakage detector, wireless seismic sensor, wireless emergency call transmitter, etc.). You can choose between English, Danish and Italian for operating and programming.

You can find more information about the Secvest 2WAY and the included components in the individual data sheets.



Product highlights:

- Entry-level package with excellent value for money
- Motion detector for indoor protection included
- Wireless magnetic contact for monitoring windows and doors
- Bidirectional wireless remote control with status query
- Proximity chip key

secvest.®

FU8007

Secvest 2WAY Base Kit (UK, DK, IT)

Technical Data

Radio frequency	868.6625 MHz, narrow band
Wireless output	10 mW
Range	approx. 30 m indoors, approx. 100 m outdoors
Emergency power supply	6 x 1.2V, 2000mAh, rechargeable NiMH batteries (type AA)
Outputs	32 wireless relay outputs, 2 wired outputs
Telephone connection	analog, optional ISDN or GSM
Dimensions (WxHxD)	285x206x45 mm
Material	ABS
Voltage	230V AC, 50/60 Hz +/- 5%
Alarm zones	48 wireless zones, 2 wired zones
Number of users	max. 50
Event memory	250 messages
Current consumption	200 mA + 10%/ - 15%
Weight	1060 g (without standby battery)