



**Part Number: 83007**

Lead Wire, #20 Str SPC, TFE Ins, AWM 1213 105C TYPE E

[Request Sample](#)

**Product Description**

High Temp Plastic Lead Wire, 20AWG (19x32) Silver Plated Copper, TFE Insulation, AWM 1213 105C TYPE E MIL-W-16878/4 600V 200C

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
20	19x32	SCC - Silver-coated Copper	1

Conductor Count:	1
Conductor Size:	20 AWG

**Insulation**

Material	Nominal Diameter	Nominal Wall Thickness
TFE - Tetrafluoroethylene	0.056 in	0.009 in

**Outer Jacket Material**

Material	Nominal Diameter
No Jacket	0.058 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR
9 Ohm/1000ft

**Current**

Element	Max. Recommended Current [A]
Mil-Std-975M Table 3.16 (single wire)	Mil-Std-975M Table 3.16 (single wire): 6.5 amps

**Voltage**

Description	Voltage Rating [V]
Mil-W-16878/4	600 V RMS Mil-W-16878/4

**Temperature Range**

UL Temp Rating:	105°C
Operating Temp Range:	-70°C To +200°C

**Mechanical Characteristics**

Bulk Cable Weight:	5 lbs/1000ft
--------------------	--------------

**Standards**

UL AWM Style:	1213
Military Specification:	NEMA HP3, MIL-W-16878/4 (Except For Stranding)

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	600 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Footnote
83007 010100	Black	
83007 0101000	Black	S W
83007 010500	Black	S W
83007 006100	Blue, Light	
83007 0061000	Blue, Light	S W
83007 006500	Blue, Light	S W
83007 001100	Brown	
83007 0011000	Brown	S W
83007 008100	Gray	
83007 0081000	Gray	S W
83007 005100	Green, Dark	
83007 0051000	Green, Dark	S W
83007 003100	Orange	
83007 0031000	Orange	S W
83007 002100	Red	
83007 0021000	Red	S W
83007 002500	Red	S W
83007 007100	Violet	
83007 0071000	Violet	S W
83007 009100	White	
83007 0091000	White	S W
83007 009500	White	S W
83007 004100	Yellow	
83007 0041000	Yellow	S W

Footnote:	S - STRIPING ADDERS FOR TYPES E AND EE: 1, 2, 3 STRIPES. MINIMUM ORDER 10,000' PER STRIPE COMBINATION. (SEE STRIPING ADDER TABLE)
Footnote:	W - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 75'.

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.