

Cordless Universal Cutter



Decoration materials, cardboard or carpet: the Xeo cordless universal cutter from Bosch enables you to effortlessly and quickly cut all different kinds of flexible materials at any time – without a cable.

Features:

- Lithium-ion technology
- No self-discharge
- No memory effect
- AutoSharp: self-sharpening blade
- Charge level indicator via LED
- Lock-off switch
- Softgrip

The Technology:



Lithium-ion technology

Thanks to its lithium-ion technology, the Xeo holds its charge even if it has not been used for months at a time.

You can recharge it at any time without any problems – regardless of whether the battery is fully charged, half charged or flat. The lithium-ion technology makes it possible to equip the Xeo with an extremely small battery.

Charge level indicator

An LED enables you to check the battery power quickly and easily.

Softgrip

Thanks to the ergonomic design with softgrip, any hand feels great with the Xeo.



Specifications	Xeo
Max. cutting strength	6 mm
No-load speed	240 rpm
Battery voltage	3.6 V
Charge time	5 hours
Cutting performance per battery charge	up to 150 m
Machine weight with battery	0.4 kg
Lock-off switch	✓
AutoSharp	✓
Part number	0 603 205 000
EAN code	3 165 140 455 121
Comes complete with:	
5-hour charger	✓ 2 607 225 243

Glue Guns



The glue guns from Bosch are ideal for adhesive attachment, model making, repairing, sealing and jointing. They stick almost anything: wood, plastic, ceramic, metal, glass, textiles, leather and much more.

The Technology:



Cordless use and mains connection

Cordless use of the Bosch Glue Gun PKP 30 LE is enabled by two rechargeable heating elements. The built-in LED display tells you whether the glue gun has been correctly placed in the charging station. The glue gun can also be connected directly to the mains for continuous operation.



Mechanical feed system

The glue feed for application can be finely regulated by means of a mechanical feed system operated by the large switch.

Bosch Constant Electronic

Automatic temperature control with electronically regulated heating elements for even glue consistency.



Features:

- Bosch Constant Electronic
- Glue stick up to 200 mm
- Mechanical feed system: fine application of glue – rapid, targeted application
- Glue stick guide with viewing glass
- Ready to use quickly thanks to glue stick pre-heating
- Practical nozzle with heat protection cladding and anti-drip device
- Wire stand makes it safe to set the glue down
- Temperature-resistant housing with protective insulation

Specifications	PKP 18 E	PKP 30 LE
Gluing capacity	20 g/min	30 g/min
Glue stick Ø	11 x 45 – 200 mm	11 x 45 – 200 mm
Voltage	100 – 240 V	220 – 240 V
Cordless use		✓
Machine weight	0.35 kg	0.37 kg
Part number	0 603 264 503	0 603 264 403
EAN code	3 165 140 078 481	3 165 140 034 562
Comes complete with:		
3 glue sticks	–	✓ 2 607 001 176
1 glue stick	✓ 2 607 001 176	–
1 universal nozzle	–	✓
1 extra-long nozzle	✓	✓

