

# PILOT LIGHT 28V 30MM SK +OPTIONS

9001SKP35LYA9

EAN Code: 3389118037502

### Main

Range of product	Harmony 9001SK	
Product or component type	Pilot light	
Device short name	9001SK	
Lens type	Domed plastic	
Light block supply	Direct 24 V AC/DC	

## Complementary

Plastic	
30 mm	
Round	
Amber	
LED	
BA 9s	
2428 V AC/DC	
0.8 N.m conforming to EN/IEC 60947-1	
Cross slotted	
Screw clamp terminals, 1 x 0.222 x 1.5 mm² conforming to EN/IEC 60947-1	
10 A	
10 A cartridge fuse conforming to EN/IEC 60947-5-1	
250 V (pollution degree 2) conforming to EN/IEC 60947-1	
2.5 kV conforming to EN/IEC 60947-1	
Any position	
54 mm	
70 mm	
42 mm	
0.082 kg	
Complete product	
Domed	
2428 V	
Yellow	
Polycarbonate	

Size	30 mm
Light source	LED

## **Environment**

Electrical shock protection class	Class II conforming to IEC 61140	
Protective treatment	тс	
IP degree of protection	IP66 conforming to IEC 60529	
NEMA degree of protection	NEMA 1	
	NEMA 12	
	NEMA 13	
	NEMA 2	
	NEMA 3	
	NEMA 3R	
	NEMA 4	
	NEMA 4X	
Vibration resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn conforming to IEC 60068-2-27	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4070 °C	
Standards	CSA C22.2 No 14	
	EN/IEC 60947-1	
	JIS C8201-5-1	
	EN/IEC 60947-5-1	
	UL 508	
	JIS C 852	
	EN/IEC 60947-5-4	
	JIS C8201-1	
Product certifications	NEMA	
	UL 508	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.572 cm
Package 1 Width	5.334 cm
Package 1 Length	9.144 cm
Package 1 Weight	226.796 g

# **Logistical informations**

Country of origin

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability

Q	Environmental footprint	
---	-------------------------	--

Environmental Disclosure

Product Environmental Profile

#### **Use Better**

Materials and Substances		
Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
REACh Regulation	REACh Declaration	


#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## 9001SKP35LYA9

### **Dimensions Drawings**

### **Dimensions**



 $\boldsymbol{e}$  panel thickness: 1 to 6 mm / 0.04 to 0.24 in.