


RASEY20-XL-N [↗](#)

Plummer block housing unit

Plummer block housing units RASEY, cast iron housing, radial insert ball bearing with grub screws in inner ring, R seals

X-life

Technical information



Your current product variant

Material	GG	Grey cast iron
Groove	N	Cast iron housing with undercut slot for end caps

Main Dimensions & Performance Data

d	20 mm	Bore diameter
L	130 mm	Length total
H 2	64 mm	Height
≈m	0.58 kg	Weight

Mounting dimensions

J	97.5 mm	Distance fixing bore
N	11 mm	Width (slot)
N 1	19 mm	Length (slot)



Dimensions

H	33.3 mm	Distance shaft axis
A	32 mm	Width (base)
A ₁	19 mm	Width (head)
H ₁	14.5 mm	Heigth (base)
B	31 mm	Width
S ₁	18.3 mm	Distance of raceway to locking collar
Q	M6	Connection thread for lubrication

Additional information

ASE04	Housing
GYE20-XL-KRR-B	Bearing designation
KASK04	Protecting cap

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.