

Product data sheet

179 N X-8/314

EAN-No. 4000896250455



314-pieces · 8 Drawers total



Application:

Efficient, mobile organisation of tools

- Tool trolley
- 7 flat and 1 high drawer
- Complete with 314-piece tool assortment in Safety-Insert-System soft foam insert

Work areas

- Much larger storage and work areas in plastic (179N) or stainless steel (179NX)
- Fully sealed work surface protects inside of trolley from leaking liquids
- Interfaces integrated in the work area for accessories such as laptop holders and top modules

Body / Pull-handle

- Extremely robust design thanks to dual-wall structure
- Complete welded construction of the entire body for tough daily workshop use
- Optimised, yielding edge protection on all four corners with real impact protection thanks to internal damping concept
- Ergonomically optimised pull handle for better manoeuvrability

Locking concept

- Ergonomically arranged side lock position for better operability protects keys and lock against damage
- Highly secure closing system with central locking technology for optimum protection of your property
- 2-stage locking
 - Central locking, lockable with cylinder lock and 2 folding keys
 - Mutual drawer locking for minimum tilting risk

Drawer concept

- Self-closing and reciprocal locking of the drawers prevents unwanted opening
- 100% sliding-out with ball-bearing telescopic slides
- Drawer design for optimum use of the interior
- Drawer fronts for optimised handling
- Dirt-resistant drawer coating for easy cleaning

High performance chassis

- Large wheels with high loading capacity, precision ball bearing and dual rounded rim in the pivot bearing, easy manoeuvrability, even with high dynamic load
- 2 swivel castors with dual brake:
 - Braked castors prevent rolling away
 - Braked swivel bearings prevent the swivel castors from turning, e.g. on inclined surfaces
- Protective ring prevents dirt and threads from getting in

EAN-No. 4000896**250455**



- Elastic castors enable smooth movement

Assistant[®] **179N-6 – 9:**

- Solvent-resistant plastic work surface
- Metal handle, powder coated in black

Assistant[®] **179NX-6 – 8:**

- Stainless steel work surface
- Extra protection through high-quality plastic end caps
- Brushed stainless steel handle
- Total loading capacity (dynamic): 540 kg
- Loading capacity (static): 1000 kg
- Loading capacity of high drawer: 25 kg
- Colour: HAZET blue
- Tool trolley Made in Germany
- Dimensions: 785 mm x 518 mm x 1020 mm
- Net weight: 89 kg
- Drawers, flat: 7 × 81 x 522 x 398 mm
- Drawers, high: 1 × 166 x 522 x 398 mm
- (Drawer) size for plastic drawer insert: 3/3+
- Worktop: Stainless steel
- Number of fixed castors: 2 (Ø 125 mm)
- Number of swivel castors: 2 (Ø 125 mm)
- Number of tools: 314

Order Number	179NX-8/314
 179NX-8	 2157-1  4968-2
 163-372/25 • ●	 863HP • 6.3 1/4  867-2 • 6.3 1/4 • 6.3 1/4  868 • 6.3 1/4 • 6.3 1/4  869 • 6.3 1/4 • 6.3 1/4
 1952-40  1976-2 2140-40	 163-513/122N                          811BML • 6.3 1/4
 666-5 730 730-3 • 730-6	 8816HP • 10 3/8  8820 • 10 3/8 • 10 3/8
 2152N/3  2154N-5	850 • 6.3 1/4 • 6.3 1/4 5.5 • 6 • 7 • 8 • 9 • 10 • 11 • 12 • 13 850E • 6.3 1/4 • 6.3 1/4 E5 • E6 • E7 • E8 • E10

Product data sheet

179 N X-8/314

EAN-No. 4000896250455



8858-2 • • •

900 • •

10 • 11 • 12 • 13 • 14 • 15 •
16 • 17 • 18 • 19 • 20 • 21 •
22 • 23 • 24 • 26 • 27 • 28 •
30 • 32

900E • •

E10 • E12 • E14 • E16 •
E18 • E20



915 •



916HP •

917-5 • •

918-10 • •



920 • •

958-2 • •

1058-2 • •

2204N • •

2 • 2.5 • 3 • 4 • 5 • 6

2208N • •

0.5 x 4 • 0.6 x 4.5 •
0.8 x 5.5 • 1 x 6

2215N • •

PH1 • PH2 • PH3

2216N • •

PZ1 • PZ2 • PZ3

2223N • •

T6 • T7 • T8 • T9 • T10 •
T15 • T20 • T25 • T27 •
T30 • T40


2223N • •

T10H • T15H • T20H •
T25H • T27H • T30H



2239N-6 • •

2250-1 • •



163-525/40



450N •

6 x 7 • 8 x 9 • 10 x 11 •
12 x 13 • 14 x 15 • 16 x 17 •
18 x 19 • 21 x 22 • 24 x 27 •
30 x 32 • 34 x 36

600N •

6 • 7 • 8 • 9 • 10 • 11 • 12 •
13 • 14 • 15 • 16 • 17 • 18 •
19 • 21 • 22 • 24 • 27 • 32

630 •

6 x 7 • 8 x 9 • 10 x 11 •
12 x 13 • 14 x 15 • 16 x 17 •
18 x 19 • 20 x 22 • 21 x 23 •
24 x 27



163-526/41N



811 •

0.4 x 2.5 • 0.5 x 3 • 0.8 x 4 •
1 x 5.5 • 1.2 x 6.5



811PH •

PH0 • PH1 • PH2



811T •

T10 • T15 • T20 • T25 •
T27 • T30



811K •

0.6 x 3.5 • 1 x 5.5



811KPH •

PH1 • PH2



811S •

0.8 x 4.5 • 1 x 5.5 • 1.2 x 7



811SPH •


PH1 • PH2 • PH3



2105LG/9H •



2116LG/8H •



163-609/61

• • • •



760-2

986 • •

4 • 5 • 6 • 7 • 8 • 9 • 10 •
12 • 14 • 17 • 19 • 22



986SL • •

4 • 5 • 6 • 7 • 8 • 9 • 10 •
11 • 12 • 14

990 • •

M5 • M6 • M8 • M10 • M12 •
M14 • M16 • M18

990LG • •

M6 • M8 • M9 • M10 • M12 •
M14

991 • •

M6 • M7 • M8 • M9 • M10 •
M12 • M14

992 • •

T20 • T25 • T27 • T30 •
T40 • T45 • T50 • T55 • T60

992SLG • •

T30 • T40 • T45 • T50 • T55

1850M-22



1841MB-33

1802M-22



2128N-1