



Main

Range	Resi9
Product or component type	Distribution block
Mounting mode	Horizontal
Accessory / separate part category	Connection accessory
Lines description	1L + N
Length in 18 mm modules	5

Complementary

Number of ways	5 ways N + 1 L
Poles configuration for 1 way	1 x 1P + N
Connection pitch	9 mm
Connector type	Plug-in
Distance between way	18 mm
Insulation	Insulated
[Ie] rated operational current	63 A at 40 °C
[Ue] rated operational voltage	230 V AC Ph/N
[Ui] rated insulation voltage	250 V AC
Mounting location	Top on plug in
9 mm pitches	10
Height	38 mm
Width	90 mm
Depth	12 mm
Colour	White (RAL 9003)
Connections - terminals	Without terminal
Range compatibility	Resi9 Resi9 XE DM Resi9 Resi9 XE ID Resi9 Resi9 XE DA Resi9 Resi9 XE PM Resi9 Resi9 XE CT Resi9 Resi9 XE TL

Environment

Standards	EN/IEC 60898
Product certifications	CE

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Minimum percentage of recycled plastic content	0