

Features

- 3.81 mm pitch
- Voltage Rating: 300V
- Current Rating: 8A
- Low Mating Force
- 2 WAY HEADER
VERTICAL
TERMINAL

RS PRO 3.81MM PITCH 2 WAY, 8A, HEADER VERTICAL TERMINAL

RS Stock No.: 0631113



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Vertical mount closed end PCB terminal block headers with a 3.81mm pitch. These 3.81mm pluggable terminal block PCB header connectors have a 300V 8A electrical rating and have green PA66 housings

General Specifications

Number of Contacts	2
Number of Rows	1
Pitch	3.81mm
Mounting Type	Through Hole
Body Orientation	Straight
Number of P	2
Termination Method	Solder
Contact Material	Brass
Contact Plating	Tin plated
Housing	PA66(UL94V-0)
Colour	Green

Electrical Specifications

Voltage Rating	300V
Current Rating	8A
Insulation Resistance	500M ohm min
Withstanding Voltage	2000V AC/minute

Mechanical Specifications

Mounting Type	Through Hole
Pitch	3.81 mm
Pin size	Please see below drawings
Pin height	3.5mm

Operation Environment Specifications

Operating Temperature	-40°C to 105°C
-----------------------	----------------

Approvals

Compliance/Certifications	RoHS Compliant, UL, CE
Declarations	Reach

Spec Drawings



