



# Datasheet

## ECP-11 Euro series

ENGLISH

11W plug-in power supply

### Features



- Input Voltage: 90 – 264Vac
- Output Power: 11W
- No Load power consumption
- UK and European versions available
- Compact and light-weight plastic case
- Protections: short circuit/overload/ overheat
- 1 year warranty
- Dimensions: 67mm x 60mm x 50mm
- Connector: 2.1 x 5.5 x 9.5mm
- Weight: 50g

Part number	Voltage	Rated Current	Voltage range	Line Regulation	Load Regulation	Ripple and Noise	MTBF
726-2763	5V	2A	4.7 ~ 5.3V	± 1%	± 5%	<10%	100,000hrs min. MIL-HDBK – 217F (25°C)
726-2772	7.5V	1.47A	7.1 ~ 7.9V				
726-2775	9V	1.22A	8.5 ~ 9.5V				
726-2779	12V	0.92A	11.4 ~ 12.6V				
726-2788	15V	0.73A	14.25 ~ 15.75V				
726-2781	18V	0.61A	17.1 ~ 18.9V				
726-2785	24V	0.46A	22.8 ~ 25.2V				

### Mechanical specification

