



Main

Range of product	Mita
Product or component type	Mini trunking
Colour tint	White
Quantity per set	45 m

Complementary

Compartment partitioning	1 compartment
Trunking dimension	38 x 25 mm
Fixing mode	Adhesive
Material	UPVC (unplasticized polyvinyl chloride)
Length	3000 Mm
Height	38 Mm
Width	25 Mm




Environment

Standards	BS 4678-4
Ambient air temperature for operation	-5...60 °C

Packing Units

Package 1 Weight	1.000 G
Package 1 Height	1.000 Mm
Package 1 width	1.000 Mm
Package 1 Length	1.000 Mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

[China RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Contractual warranty

Warranty

18 months

Product Life Status :	Commercialised
-----------------------	-----------------------