

PP FO CABL-60M-2xPP Metal LCD OV MM50



Image is for illustration purposes only. Please refer to product description.

Part number	33 58 231 0600 027
Specification	PP FO CABL-60M-2xPP Metal LCD OV MM50
HARTING eCatalogue	https://harting.com/33582310600027

Identification

Category	System cabling
Series	HARTING PushPull (V4)
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING PushPull (V4)
Connector 2	HARTING PushPull (V4)
Type of cable	FO cable
Description of the cable	Multimode

Version

Cable length	60 m
Core structure	50 / 125 µm

Technical characteristics

Limiting temperature	-40 ... +70 °C
Degree of protection acc. to IEC 60529	IP65 / IP67
Cable diameter	6.5 mm

Material properties

Material (hood/housing)	Metal
Material (cable)	PUR (polyurethane)
RoHS	compliant
ELV status	compliant



Pushing Performance
 Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
----------------	--------------------------------

Commercial data

Packaging size	1
Net weight	104 g
Country of origin	Czechia
European customs tariff number	85447000
GTIN	5713140153974
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600