



Vertical partition between sections D: 600 mm

Model	
product brand name	SIVACON S4
product designation	section division
design of the surface	other
General technical data	
design	assembly kit
suitability for use	for main busbar at top/bottom
RAL color number	other
color	miscellaneous
Product details	
product component	
• cable entry	No
• lock	No
Mechanical Design	
height	1 900 mm
width	1 mm
depth	600 mm
installation width for cabinet installation	1 mm
installation depth for cabinet installation	600 mm
shape of inner subdivisions	
• shape 2a	Yes
• shape 2b	Yes
• shape 3a	No
• shape 3b	No
• shape 4a	No
• shape 4b	No
mounting position	vertical
net weight	8.1 kg
material	sheet-steel
Certificates	
reference code according to IEC 81346-2	UC
Approvals Certificates	
General Product Approval	other



[Miscellaneous](#)



[Confirmation](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ3000-0BA16>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ3000-0BA16>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ3000-0BA16

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/4/2025 

