

Datasheet

RS Pro Eyebolt M20

RS Stock No: **673-664**



Product Details

RS Pro eyebolt with M20 thread size, is suitable for use in a wide range of lifting applications. This eyebolt is proof tested and supplied completely with test certificate. It is a high quality metric eyebolt with collar to BS4278. This eyebolt made of carbon steel, has a diameter of 15 mm.

Features and Benefits

- M10 thread size
- 15 mm thread length
- Made of carbon steel
- 1.6t working load limit



Specifications:

Diameter	27 mm
Material	Carbon Steel
Thread Length	32 mm
Thread Size	M20
Working Load Limit	1.6 t
Collar Diameter	40 mm
Collar Thickness	14 mm
Eye Outside Diameter	59 mm
Overall Height	97 mm
Standards Met	BS 4278:1984