

MTS SPORTY RANGE

MTS FIT

S3S SR FO HI CI ESD



DESCRIPTION

Based in southwest France since the company was founded in 1955, ANNIC SAS, better known as MTS More Than Safety is today one of Europe's foremost safety Footwear brands under the Honeywell portfolio. Introducing a sports line designed exclusively by MTS: the unique design and colours of MTS Sporty Range models combine aesthetics research, ergonomics and technological efficiency. As a result: a high-performance look and hightech materials, inspired by high-level sports. MTS Fit S3S is a non-metallic safety shoe with a composite toe and an SR rated slip resistant outsole. Made in France and manufactured according to ISO 9001.



MTS Fit

FEATURES

- Suitable for Indoor/Outdoor use
- Ideal for: Logistics, Services, Warehouses and Transportation industries
- Composite toe cap protects against impact and compression
- Flexible and lightweight non metallic safety shoe, casual sporty design
- TPU heel counter for increased support, flexibility and comfort
- Heel counter lining made of onMicro Suede for more durability and stability
- Dual-density injected PU outsole – enhances grip, ultralight, oil resistant, slip resistant, HI-CI and silicone-free to meet painting requirements in the automotive industry; free from paint wetting impairment substances
- ESD marking
- Accessory: Modular three width Insock Fitting System: standard, wide or narrow – increases the comfort from wearing the shoe



Antistatic properties



Anti-puncture resistance
with PS level



Heel energy absorption



Cleated outsole SR:
Excellent Slip Resistance



Resistance to fuel oil



Heat Insulated Sole,
Cold Insulated Sole.



ESD: Certification of
Electrical resistance

TECHNICAL SPECIFICATIONS

Upper	onDura Nilo Black, onSuede 0,7 inches, water-resistant and breathable
Lining	Red colour full Artico lining and onMicro Suede black on Heel counter
Fastening	Flat elastic laces
Toe Cap	Toe cap resistant to an impact of 200 Joules, Composite Toe Cap
Midsole	Anti-perforation, non-metallic onPROTECTOR DIAMOND, type PS
Insock	Thermoformed PU foam, anatomic, antistatic, TITAN
Sole	Dual density injected PU outsole, oil resistant FO, antistatic, ESD
Sole pattern	Multi-purpose, slip resistance conforms to SR standard
Weight (per one shoe)	Approximately 1,433 pounds
Colors	Black Red
Sizes	4-16
Standard	ASTM F2413-18, ASTM F3445-21, EN ISO 20345:2022, S3S SR FO HI CI ESD
Style	Low-cut

ORDERING INFORMATION

DESCRIPTION	REF. IN SAP	SIZE
MTS Fit	6270616	4-16

For More Information

automation.honeywell.com

For Information on Innovations and Patents

hsmpats.com

Honeywell Safety Products USA, Inc.

855 S Mint St, Charlotte, NC 28202

www.honeywell.com

