

Electronic housing - UM108-SE - 2959476

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Side element, 5 mm wide, PCB width: 107.5 mm



Why buy this product

- Lateral elements with potential ground contact available from the PCB to the DIN rail (EMC)
- Inexpensive as a result of reducing the number of separate housing parts
- Flexible size and shape
- Fast assembly on standard NS 35 or NS 32 DIN rails
- Wide range of options for external conductor connection
- High degree of mechanical stability by screwing the lateral elements to the profile
- The modules can be marked with Phoenix Contact marking material using the marking grooves in the press-drawn section

Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 086138
Weight per Piece (excluding packing)	6.48 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

General

Housing type	Panel mounting base
Housing material	PA
Color	green

Technical data

Inflammability class according to UL 94	V0
---	----

Classifications

eCl@ss

eCl@ss 4.0	27180401
------------	----------

Electronic housing - UM108-SE - 2959476

Classifications

eCl@ss

eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000721

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized 
