

Crimping pliers - CRIMPFOX-TC 10 - 1212114

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Crimping pliers, for turned contacts, 6.0 - 10 mm², square crimp, incl. contact locator



Why buy this product

- Marked die stations for precise processing of corresponding cross sections
- Crimping pliers for processing turned contacts
- The integrated positioning tool ensures that the contacts are perfectly aligned in the die



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 454025
Weight per Piece (excluding packing)	724.5 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

General

Color	black
Compression	Square crimp
Type of contact	Turned contacts
Name	Crimping position 1
Max. cross section	6 mm ²
AWG max	10

Crimping pliers - CRIMPFOX-TC 10 - 1212114

Technical data

General

Name	Crimping position 2
Max. cross section	10 mm ²
AWG max	8
Name	Crimping position 3
Die station	Crimping position 4
	Crimping position 5

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

GOST

Ex Approvals

Crimping pliers - CRIMPFOX-TC 10 - 1212114

Approvals

Approvals submitted

Approval details

GOST 

Accessories

Accessories

Die

Replacement die - CRIMPFOX-TC 10/DIE - 1212296



Spare die for CRIMPFOX-TC 10

Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring
