

FEATURES

- **Nylon Material:** Provides excellent strength and durability for long-term use
- **Non-Releasable Design:** Ensures a secure and permanent fastening solution
- **Length of 203mm:** Suitable for bundling larger cable groups
- **Width of 4.6mm:** Offers a balance between flexibility and strength
- **Maximum Bundle Diameter of 52mm:** Accommodates a wide range of cable sizes
- **Tensile Strength of 22kg:** Supports heavy-duty applications
- **UL 94 V-0 Fire Behaviour:** Meets stringent fire safety standards
- **RoHS Compliant:** Ensures adherence to environmental and safety regulations

RS PRO 203mm Nylon Cable Tie, Non-Releasable

RS Stock No: 656-037



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a durable and reliable cable tie solution designed for securing and organising cables efficiently. This non-releasable cable tie is ideal for applications requiring a strong and permanent hold, ensuring cables remain securely fastened.

General Specifications

Colour	White
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	22 kg

Protection Category

Fire Behaviour	UL 94 V-0
UV Resistant	No

Mechanical Specifications

Length	203 mm
Material	Nylon
Maximum Bundle Diameter	52 mm
Width	4.6 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	RoHS, UL94V-0
---------------------	---------------

