

KERN HN-D.

Pen-Type-Härteprüfgerät nach Leeb zur mobilen Härteprüfung von Metallen



Measuring system

Measuring range (Max):	999
Measuring range (Min):	0
Precision (of [Max]):	1 %
Readout:	1
Sensor:	D
Weighing units:	HB HL HRB HRC HV MPa

Display

Display digit height:	9 mm
Display digit height:	5 mm

Functions

All measurement directions possible (360°):	yes
Obtaining average:	yes
Statistical function:	yes
Wireless printer connection:	yes

Environmental conditions

Maximum operating temperature:	60 °C
Minimum ambient temperature:	-10 °C

Power supply

Charging time:	3 h
Input voltage:	100 - 240 V
n/a:	EURO

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	16 h
---------------------------------	------

Service

ISO calibration certificate:	961-131
------------------------------	---------

Category

Brand:	Sauter
Category:	Hardness testers
Product Group:	Electronic Leeb hardness tester

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	255 x 215 x 73 mm
Gross weight:	1,134 kg
Net weight:	160 g
Shipping method:	Parcel service
UN number:	3481

Construction

Overall dimensions mounted (WxDxH):	147 x 35 x 22 mm
-------------------------------------	------------------