



Datasheet

EN

RS Pro RS-125 Embedded Industrial 5 Port PoE+ 10/100 Ethernet Switch

Stock Number: 2263244



Specifications:

- Power Consumption: 4 Watts Max : 220 mAmps@+5VDC/36mAmps@+30VDC
- PoE Power Budget: 90W @ 70°C
- Power Supply input: Unregulated +44V to +57Volts DC, reverse polarity protection
- Operating Temperature: -40°C to +70°C/-40°F to +158°F
- Ethernet Ports: 5 x RJ45 jack, 10/100Mhz autosensing, crossover auto sensing (Auto MDIX)
- Ports 1-4 IEEE 802.3 af/at compliant: deliver up to 30W to each port
- Unmanaged 10/100Mbps Ethernet
- Housing: This device is uncased for embedded applications. The mounting holes are connected to Functional Earth
- Weight: 0.182 kg / 6.4 oz.
- Packaged Dimensions: 160x135x49 mm / 6.3x5.3x1.9 in.

Features:

- 5 Port PoE+ 10/100 Mbs Ethernet Switch
- Redundant dual power inputs: +44V to +57Volts DC
- No software required - Simply plug in and connect
- Industrial temperature range

