

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0349674001](#)
Status: **Active**
Overview: [Mini50™ Connection Systems](#)
Description: Mini50™ Sealed Receptacle, Single Row, with CPA, 4 Circuits, Polarization Option A, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-31301-898 \(PDF\)](#) [Product Literature \(PDF\)](#)

General

Product Family	Crimp Housings
Series	34967
Application	Power, Sealed, Wire-to-Board
Overview	Mini50™ Connection Systems
Polarization	A
Product Literature Order No	987651-6273
Product Name	Mini50™ Sealed
UPC	887191620381

Physical

Circuits (maximum)	4
Color - Resin	Black
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	2.765/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-31301-898
Sales Drawing	349674000-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

[34967 Series](#)

Mates With

Contact Molex for mating information.

Use With

CTX50 Sealed Receptacle Terminal
[34905-2443](#) , [34905-2444](#)