

Snap-in markers - UCT-EMP (40X17) - 1014120

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Snap-in markers, Sheet, white, unlabeled, can be labeled with: THERMOMARK CARD, BLUEMARK CLED, BLUEMARK LED, TOPMARK LASER, Mounting type: snapped into marker carrier, Lettering field: 40 x 17 mm

Why buy this product

- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The format automatically ensures printing with a high degree of positioning accuracy
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and precisely using the THERMOMARK CARD and the BLUEMARK LED

Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 783019
Weight per Piece (excluding packing)	7.25 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	40 mm
Width (a)	17 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Note	Can be labeled via thermal transfer
Color	white
Components	free from silicone, halogen, and cadmium
Inflammability class according to UL 94	V0
Material	PC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	3

Snap-in markers - UCT-EMP (40X17) - 1014120

Technical data

General

Number of individual labels per row	1
Marking mounting type	snapped into marker carrier

Classifications

eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410