

Features

- End cutter, ideal for hard-to-reach areas. It cuts the component lead at 1.5mm from the surface.
- For copper wire Ø 1.30mm (16 awg)
- Steel thickness 5mm.
- Anti-reflection phosphating surface treatment
- Anti-slip bi-material dolphin handle with light and comfortable grip
- Made in Italy

RS PRO Standoff Flush Cutter, Medium

RS Stock No.: 0616317



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Buy this product from <https://uk.rs-online.com/>

RS PRO Standoff Flush Cutter

RS PRO cutter has flush end cutter, ideal for specific electronics applications. It cuts the component lead at 1.5mm from the surface.

For copper wire Ø 1.30mm (16 awg) Steel thickness 5mm. Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.

Made with high carbon steel and undergo a controlled atmosphere heat treatment. The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.

The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator.

General Specifications

Cutter Type	Standoff Flush cutter
Materials Cut	Copper Wire Ø 1.30mm (16 awg)
No Sparking	No
Overall Length	148mm +/- 2mm
VDE/1000V Approved	No
Height Safe	No
ESD Safe	No
Material	High Carbon Steel
Maximum Cutting Capacity	1.30mm
Cut Type	Flush

Approvals

Declarations	REACH DoC
--------------	-----------

